


Film, Double Metallized Polypropylene, Commercial Grade, R76, 0.022 uF, 5%, 1,600 V, 85C, Lead Spacing = 22.5mm



#### Dimensions

L	26.5mm +0.3mm
H	15mm +0.1mm
T	6mm +0.2mm
S	22.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

#### Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	500

#### General Information

Dielectric:	Double Metallized Polypropylene
Style:	Radial
Series:	R76
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	AEC-Q200
AEC-Q200:	Yes
Miscellaneous:	Voltage Derating: 1.35%/C Above 75C (AC), 1.25%/C Above 85C (DC)

#### Specifications

Capacitance:	0.022 uF
Capacitance Tolerance:	5%
Voltage DC:	1600 VDC
Voltage AC:	650 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.1% 1kHz, 0.06% 10kHz, 0.1% 100kHz
Insulation Resistance:	100 GOhms
Max dVdt:	3,000 V
Inductance:	18 nH