


KEMET Part Number: SC-15-100
(UALSC151000000)

Choke, SC, 1000 uH



Dimensions

L	49mm MAX
T	27mm MAX
H	49mm MAX
S	35mm MAX
S1	35mm NOM
LL	15mm +/-2mm
Wire Size	1.8mm

Packaging Specifications

Weight:	100 g
----------------	-------

General Information

Style:	Through-Hole Toroid
Series:	SC
Description:	Standard Common Mode Filter
RoHS:	Yes
Miscellaneous:	Inductance Measurement Condition: 100kHz 1mA KC547
Notes:	Lead Spacing (S/S1) Are For Reference Only.

Specifications

Inductance:	1000 uH
Rated Temperature:	105C
Current:	15 Amps
Voltage AC:	250 VAC
DC Resistance:	12 mOhms
Insulation Resistance:	100 MOhms