
## **KEMET Part Number: SS11H-07120-CH**

(UAL11H07120CH0)



## Commercial Grade, SS11V/H-CH, 0.012 H



Dimensions		
L	21mm +/-1mm	
Т	20.5mm +/-1mm	
Н	16mm +/-1mm	
S	14mm +/-0.5mm	
S1	18mm +/-0.5mm	
LL	3.5mm +/-1mm	
F	0.8mm NOM	

Packaging Specifications		
Weight:	10.8 g	

General Information		
Style:	Through-Hole Choke	
Series:	SS11V/H-CH	
Description:	Common Mode Filter	
RoHS:	Yes	
Miscellaneous:	Inductance Measurement Condition: 1kHz 1V KC530	

Specifications		
Inductance:	12000 uH	
Rated Temperature:	120C	
Current:	0.7 Amps	
Voltage AC:	250 VAC	
DC Resistance:	900 mOhms	
Insulation Resistance:	100 MOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

