

KEMET Part Number: T491A105K016AT
(B45196E3105K109)



Tantalum, MnO2 Tantalum, T491, 1 uF, 10%, 16 V, 3216, SMD, MnO2, Molded, 10 Ohms, Height Max = 1.8mm



| General Information | |
|---------------------|-------------------|
| Dielectric: | MnO2 Tantalum |
| Style: | SMD Chip |
| Series: | T491 |
| Description: | SMD, MnO2, Molded |
| RoHS: | Yes |
| Termination: | Tin |

| Specifications | |
|------------------------|--|
| Capacitance: | 1 uF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 16 VDC (85C), 10.72 VDC (125C) |
| Temperature Range: | -55/+125C |
| Dissipation Factor: | 4% 120Hz 20C |
| Failure Rate: | N/A |
| Resistance: | 10 Ohms (100kHz) |
| Current: | 87 mAmps (100kHz 25C), 78.3 mAmps (85C), 34.8 mAmps (125C) |
| Leakage Current: | 0.5 uAmps (5min 20C) |

| Dimensions | |
|------------|-------------------|
| Footprint | 3216 |
| L | 3.2mm +/-0.2mm |
| W | 1.6mm +/-0.2mm |
| H | 1.6mm +/-0.2mm |
| T | 0.13mm REF |
| S | 0.8mm +0.2/-0.3mm |
| F | 1.2mm +/-0.1mm |
| A | 1.2mm MIN |
| B | 0.4mm +/-0.15mm |
| E | 1.3mm REF |
| G | 1.1mm REF |
| P | 0.4mm REF |
| R | 0.4mm REF |
| X | 0.1mm +/-0.1mm |

| Packaging Specifications | |
|--------------------------|------------|
| Weight: | 58.6 mg |
| Packaging: | T&R, 178mm |
| Packaging Quantity: | 2000 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2017 IntelliData.net