

KEMET Part Number: T491A155K016AT
(B45196E3155K109)

Tantalum, MnO2 Tantalum, T491, 1.5 uF, 10%, 16 V, 3216, SMD, MnO2, Molded, 8 Ohms, Height Max = 1.8mm



Dimensions

Footprint	3216
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	1.6mm +/-0.2mm
T	0.13mm REF
S	0.8mm +0.2/-0.3mm
F	1.2mm +/-0.1mm
A	1.2mm MIN
B	0.4mm +/-0.15mm
E	1.3mm REF
G	1.1mm REF
P	0.4mm REF
R	0.4mm REF
X	0.1mm +/-0.1mm

Packaging Specifications

Weight:	58.6 mg
Packaging:	T&R, 178mm
Packaging Quantity:	2000

General Information

Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Series:	T491
Description:	SMD, MnO2, Molded
RoHS:	Yes
Termination:	Tin

Specifications

Capacitance:	1.5 uF
Capacitance Tolerance:	10%
Voltage DC:	16 VDC (85C), 10.72 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	6% 120Hz 20C
Failure Rate:	N/A
Resistance:	8 Ohms (100kHz)
Current:	97 mAmps (100kHz 25C), 87.3 mAmps (85C), 38.8 mAmps (125C)
Leakage Current:	0.5 uAmps (5min 20C)