

KEMET Part Number: T491A336K004AT
(B45196H0336K109)

Tantalum, MnO₂ Tantalum, T491, 33 uF, 10%, 4 V, 3216, SMD, MnO₂, Molded, 3 Ohms, Height Max = 1.8mm



Dimensions

Footprint	3216
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	1.6mm +/-0.2mm
T	0.13mm REF
S	0.8mm +0.2/-0.3mm
F	1.2mm +/-0.1mm
A	1.2mm MIN
B	0.4mm +/-0.15mm
E	1.3mm REF
G	1.1mm REF
P	0.4mm REF
R	0.4mm REF
X	0.1mm +/-0.1mm

Packaging Specifications

Weight:	58.6 mg
Packaging:	T&R, 178mm
Packaging Quantity:	2000

General Information

Dielectric:	MnO ₂ Tantalum
Style:	SMD Chip
Series:	T491
Description:	SMD, MnO ₂ , Molded
RoHS:	Yes
Termination:	Tin

Specifications

Capacitance:	33 uF
Capacitance Tolerance:	10%
Voltage DC:	4 VDC (85C), 2.68 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	6% 120Hz 20C
Failure Rate:	N/A
Resistance:	3 Ohms (100kHz)
Current:	137 mAmps (100kHz 25C), 123.3 mAmps (85C), 54.8 mAmps (125C)
Leakage Current:	1.3 uAmps (5min 20C)