


**KEMET Part Number: T491D475K050AT**  
(B45196E7475K409)

Tantalum, MnO<sub>2</sub> Tantalum, T491, 4.7 uF, 10%, 50 V, 7343, SMD, MnO<sub>2</sub>, Molded, 1.2 Ohms, Height Max = 3.1mm



General Information	
Dielectric:	MnO <sub>2</sub> Tantalum
Style:	SMD Chip
Series:	T491
Description:	SMD, MnO <sub>2</sub> , Molded
RoHS:	Yes
Termination:	Tin

Specifications	
Capacitance:	4.7 uF
Capacitance Tolerance:	10%
Voltage DC:	50 VDC (85C), 33.5 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	6% 120Hz 20C
Failure Rate:	N/A
Resistance:	1.2 Ohms (100kHz)
Current:	354 mAmps (100kHz 25C), 318.6 mAmps (85C), 141.6 mAmps (125C)
Leakage Current:	2.4 uAmps (5min 20C)

Dimensions	
Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	2.8mm +/-0.3mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
A	3.6mm MIN
B	0.5mm +/-0.15mm
E	3.5mm REF
G	3.5mm REF
P	0.9mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Packaging Specifications	
Weight:	446.84 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500