

KEMET Part Number: C1206C103J3GACTU
(C1206C103J3GAC7800)

Ceramic, Commercial-(CxxxxC), 0.01 uF, 5%, 25 V, 1206, COG, SMD, MLCC, Ultra-Stable, Low Loss, Class I



General Information

Style:	SMD Chip
Series:	Commercial-(CxxxxC)
Chip Size:	1206
Description:	SMD, MLCC, Ultra-Stable, Low Loss, Class I
Features:	Ultra-Stable, Low Loss, Class I
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A

Dimensions

L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
T	1mm +/-0.10mm
B	0.5mm +/-0.25mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	2500

Specifications

Capacitance:	0.01 uF
Capacitance Tolerance:	5%
Voltage DC:	25 VDC
Dielectric Withstanding Voltage:	62.5 V
Temperature Range:	-55/+125C
Temperature Coefficient:	COG
Dissipation Factor:	0.1%
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	100 GOhms