

Tantalum, Polymer Tantalum, T520, 22 uF, 20%, 6.3 V, 3216, SMD, Polymer, Molded, Low ESR, Non-Combustible, 90 mOhms, Height Max = 1.8mm



**Dimensions**

Dimensions	
Footprint	3216
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	1.6mm +/-0.2mm
T	0.13mm REF
S	0.8mm +/-0.3mm
F	1.2mm +/-0.1mm
A	1.2mm MIN
P	0.4mm REF
R	0.4mm REF
X	0.1mm +/-0.1mm

**Packaging Specifications**

Weight:	53.16 mg
Packaging:	T&R, 178mm
Packaging Quantity:	2000

**General Information**

Dielectric:	Polymer Tantalum
Style:	SMD Chip
Series:	T520
Description:	SMD, Polymer, Molded, Low ESR, Non-Combustible
Features:	Low ESR
RoHS:	Yes
Termination:	Tin

**Specifications**

Capacitance:	22 uF
Capacitance Tolerance:	20%
Voltage DC:	6.3 VDC (105C)
Temperature Range:	-55/+105C
Dissipation Factor:	8% 120Hz 25C
Failure Rate:	N/A
Resistance:	90 mOhms (100kHz 25C)
Current:	1100 mAmps (100kHz 45C), 770 mAmps (85C), 275 mAmps (105C)
Leakage Current:	13.9 uA (5min 25C)