

KEMET Part Number: C1206T106K4RCLTU
(C1206T106K4RCL7800)

Ceramic, COTS, COTS-(CxxxxT), 10 uF, 10%, 16 V, 1206, X7R, SMD, MLCC, COTS, Temperature Stable, Class II



Dimensions

L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
T	1.6mm +/-0.20mm
B	0.5mm +/-0.25mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	2000

General Information

Style:	SMD Chip
Series:	COTS-(CxxxxT)
Chip Size:	1206
Description:	SMD, MLCC, COTS, Temperature Stable, Class II
Features:	Temperature Stable, Class II
RoHS:	No
Termination:	Lead (SnPb)
Marking:	No
Failure Rate:	N/A
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours

Specifications

Capacitance:	10 uF
Capacitance Tolerance:	10%
Voltage DC:	16 VDC
Dielectric Withstanding Voltage:	40 V
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	10%
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	1 MOhms