


Aluminum Electrolytic, 105C, ESH, 1000 uF, 20%, 35 V, -40/+105C, Lead Spacing = 5mm



Note: '()' correspond to the letters used in the product bulletin

#### Dimensions

D	13mm +/-0.5mm
L	25mm +2mm
S	5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	20mm MIN
F	0.6mm NOM

#### Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	1600

#### General Information

Dielectric:	Aluminum Electrolytic
Series:	ESH
Description:	High CV Single Ended Aluminum Electrolytic
Features:	High CV
RoHS:	Yes
Lead:	Wire Leads

#### Specifications

Capacitance:	1000 uF
Capacitance Tolerance:	20%
Voltage DC:	35 VDC, 44 VDC (Surge)
Temperature Range:	-40/+105C
Rated Temperature:	105C
Life:	2000 Hrs
Dissipation Factor:	14%
Current:	995 mAmps (120Hz 105C)
Leakage Current:	350 uA (2min 20C)
Impedance Ratio at -25C:	2
Impedance Ratio at -40C:	3