

Film, Metallized Polypropylene, Safety, F862, 0.1 uF, 10%, 630 V, 310 V, 110C, Lead Spacing = 15mm



General Information	
<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Radial
<b>Series:</b>	F862
<b>Features:</b>	MKP EMI, AEC-Q200, Heavy Duty, Cap.Pow.Supply
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Approvals:</b>	ENEC, UL, cUL, CQC
<b>AEC-Q200:</b>	Yes
<b>Miscellaneous:</b>	ClimCat: 40/110/56/B

Dimensions	
<b>L</b>	18mm MAX
<b>H</b>	13.5mm MAX
<b>T</b>	7.5mm MAX
<b>S</b>	15mm +/-0.4mm
<b>LL</b>	25mm +5mm
<b>F</b>	0.8mm +/-0.05mm
<b>G</b>	0.5mm NOM

Specifications	
<b>Capacitance:</b>	0.1 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	630 VDC
<b>Voltage AC:</b>	310 VAC
<b>Temperature Range:</b>	-40/+110C
<b>Rated Temperature:</b>	110C
<b>Dissipation Factor:</b>	0.3% 1kHz
<b>Insulation Resistance:</b>	30 GOhms
<b>Max dVdt:</b>	400 V
<b>Safety Class:</b>	X2

Packaging Specifications	
<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	800