

Film, Metallized Polypropylene, Safety, F862, 1.2 uF, 10%, 630 V, 310 V, 110C, Lead Spacing = 22.5mm



General Information	
Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	F862
Features:	MKP EMI, AEC-Q200, Heavy Duty, Cap.Pow.Supply
RoHS:	Yes
Lead:	Wire Leads
Approvals:	ENEC, UL, cUL, CQC
AEC-Q200:	Yes
Miscellaneous:	ClimCat: 40/110/56/B

Dimensions	
L	26mm MAX
H	22mm MAX
T	13mm MAX
S	22.5mm +/-0.4mm
LL	17mm -1mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Specifications	
Capacitance:	1.2 uF
Capacitance Tolerance:	10%
Voltage DC:	630 VDC
Voltage AC:	310 VAC
Temperature Range:	-40/+110C
Rated Temperature:	110C
Dissipation Factor:	0.2% 1KHz
Insulation Resistance:	10 GOhms
Max dVdt:	200 V
Safety Class:	X2

Packaging Specifications	
Packaging:	Pizza
Packaging Quantity:	300