

Ceramic, High Q, Microwave (CBR), 39 pF, 5%, 50 V, 0402, COG, SMD, Fixed, RF, Ultra High Q, Low ESR, Class I



**Dimensions**

<b>L</b>	1mm +/-0.05mm
<b>W</b>	0.5mm +/-0.05mm
<b>T</b>	0.5mm +/-0.05mm
<b>B</b>	0.25mm +0.05/-0.1mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	10000

**General Information**

<b>Style:</b>	SMD Chip
<b>Series:</b>	Microwave (CBR)
<b>Chip Size:</b>	0402
<b>Description:</b>	SMD, Fixed, RF, Ultra High Q, Low ESR, Class I
<b>Features:</b>	Ultra High Q, Low ESR, Class I
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Marking:</b>	No
<b>Miscellaneous:</b>	Minimum Q = 1400
<b>Notes:</b>	Solder Reflow Only

**Specifications**

<b>Capacitance:</b>	39 pF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage DC:</b>	50 VDC
<b>Dielectric Withstanding Voltage:</b>	125 V
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	COG
<b>Dissipation Factor:</b>	0.1%
<b>Aging Rate:</b>	0% Loss/Decade Hour
<b>Insulation Resistance:</b>	10 GOhms
<b>Quality Factor:</b>	1400

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.