

KEMET Part Number: T540B107M004AH6610
(04051-012A)



Tantalum, Polymer Tantalum, COTS, T540_COTS, 100 uF, 20%, 4 V, 3528, SMD, Polymer, Molded, COTS, N/A, 80 mOhms, Height Max = 2mm



Dimensions	
Footprint	3528
L	3.5mm +/-0.2mm
W	2.8mm +/-0.2mm
H	1.9mm +/-0.1mm
T	0.13mm REF
S	0.8mm +/-0.3mm
F	2.2mm +/-0.1mm
A	1.9mm MIN
B	0.4mm +/-0.15mm
E	2.2mm REF
G	1.8mm REF
P	0.5mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Packaging Specifications	
Weight:	98.3 mg
Packaging:	T&R, 178mm
Packaging Quantity:	2000

General Information	
Dielectric:	Polymer Tantalum
Style:	SMD Chip
Series:	T540_COTS
Description:	SMD, Polymer, Molded, COTS
Features:	Non-Combustible, Low ESR, COTS
RoHS:	No
Termination:	Solder Coated
Approvals:	DLA Drawing 04051
Notes:	In Polarity Stripe, At KEMET's Option, Type May Be Indicated: No Symbol = Standard (Or Low Leakage) MnO ₂ Tantalum Chip, O = LowESR T494, R = Low ESR T495, F = Fused T496, HT = 150C Rated T498 (or B45196P, B45198P), H = 175C rated T499, M = Multiple Anode

Specifications	
Capacitance:	100 uF
Capacitance Tolerance:	20%
Voltage DC:	4 VDC (85C), 2.68 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	8% 120Hz 25C
Failure Rate:	N/A
Resistance:	80 mOhms (100kHz 25C)
Current:	1260 mAmps (100kHz 45C)
Leakage Current:	40 uA (5min 25C)
Testing and Reliability:	10 Cycles Surge Current Testing At +25C +/-5C After Voltage Aging

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

