


Varistors, VP, Plastic Encapsulated, 200 V, 150 VAC, 240 V, 395 V, 5 A, 400 A, 9 J, 100 mW



Dimensions

Chip Size	3225
L	8mm +/-0.5mm
W	6.3mm +/-0.4mm
H	3.4mm +/-0.3mm
F	3mm +/-0.3mm
B	1.5mm +/-0.3mm
K	1.7mm +/-0.3mm

Packaging Specifications

Packaging:	T&R
Packaging Quantity:	1500

General Information

Type:	Varistors
Style:	SMD Molded
Series:	VP
Description:	Surface Mount Varistors
Features:	Plastic Encapsulated
Termination:	Nickel Tin
RoHS:	Yes
Approvals:	UL

Specifications

Voltage DC:	200 VDC (25C)
Voltage AC:	150 VAC
Temperature Range:	-40/+85C
Storage Temperature Range:	-40/+125C
Varistor Voltage:	240 VDC at 1 mAmps
Clamping Voltage:	395 V
Clamping Current:	5 Amps (8/20 us MAX)
Surge Current:	400 Amps (8/20 us MAX)
Energy:	9 J (10/1000 us MAX)
Capacitance:	140 pf (1kHz)