


JWPS CONNECTOR

4.0mm pitch/Disconnectable Crimp style connectors

(Combined use for both wire-to-board and wire-to-wire connections)



This JWPS connector can be used for the place of which especially waterproof is required.

This is the wire-to-board connector that is grade 7 ingress protection of JIS C 0920 (IPX7 of IEC 60529).

- · Waterproof performance
- Contained seal ring
- · Solid rubber seal
- Double-spring construction
- Housing-to-terminal locks
- Mis-mating prevention key

Specifications -

• Current rating: 4 A AC, DC (AWG #22)

: 5 A AC, DC (AWG #20) : 6 A AC, DC (AWG #18)

• Voltage rating: 300 V AC, DC

• Temperature range: -55°C to +85°C

(including temperature rise in applying

electrical current)

 Applicable wire: Conductor size/ AWG #22 to #18 Insulation O.D./ 1.75 to 2.5 mm

Applicable PC board thickness: 1.6 mm

• Waterproof grade: Grade 7 ingress protection of JIS C 0920

(IPX7 of IEC 60529)

(*Since the waterproof performance is not available at the opposite side of mating entrance, waterproof treatment is required,

if necessary.)


- * Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.
- * Contact JST for details.
- * Compliant with RoHS.


Standards-

Recognized E60389

A Certified R50218382

PC board layout and Assembly layout






Note: 1. The above figure is the figure viewed from the connector mounting side.

2. Hole dimensions differ according to the type of PC board and piercing method.

The dimensions above should serve as a guideline. Contact JST for details

JWPS CONNECTOR

Receptacle contact



Model No.	Applicable wire AWG#	Insulation O.D. (mm)	Q'ty/ reel
SJWPSR-21T-P1.0	22~18	1.75~2.5	4,500


Material and Finish

Copper alloy, tin-plated

RoHS compliance

	Crimping machine	Applicator			
		Crimp applicator	Dies	Crimp applicator with dies	
SJWPSR-21T-P1.0	AP-K2N	MKS-L	MK/SJWPSR/T-21-10	APLMK SJWPSR/T21-10	
SJWPSR-211-P1.0		_	_	_	

Receptacle housing assembly



Circuits	Keying	Model No.	Q'ty/box
	Х	04R-JWPS-VKLE-DX-A	400
4	Υ	04R-JWPS-VSLE-DY-A	400
	Z	04R-JWPS-VELE-DZ-A	400


Material

Receptacle housing: Glass-filled PBT, UL94V-0, X-Keying (black), Y-Keying (natural), Z-Keying (blue) Retainer: PBT, UL94V-0, purple Seal rubber plate: Silicone rubber, light blue

RoHS compliance

Note: Seal rubber plate and retainer are preassembled in receptacle housing assembly.

Header housing assembly



	Circuits	Keying	Model No.	Q'ty/box
	4	Х	S04B-JWPS-KKS-XR	160
		Υ	S04B-JWPS-KSS-YR	160
		Z	S04B-JWPS-KES-ZR	160

Material and Finish

Header housing: Glass-filled PBT, UL94V-0, black Seal ring holder: Glass-filled PBT, UL94V-0, X-Keying (black), Y-Keying (natural), Z-Keying (blue) Seal ring: Silicone rubber, brown

Tab contact: Copper alloy, tin-plated

RoHS compliance This product displays (LF)(SN) on a label.

Note: Seal ring and seal ring holder are preassembled in header housing assembly.