


Tantalum, MnO2 Tantalum, COTS Reduced Volume, T428_COTS, 390 uF, 10%, 6.3 V, 7260, SMD, MnO2, High CV, Molded, COTS, Face Down, A (Non-ER), 130 mOhms, Height Max = 3.5mm



Dimensions

Footprint	7260
L	7.2mm +/-0.4mm
W	6mm +/-0.3mm
H	3.5mm MAX
S	1.6mm +/-0.2mm
F	4.95mm +/-0.2mm
R	1.6mm +/-0.2mm

Packaging Specifications

Weight:	860 ug
Packaging:	T&R, 178mm
Packaging Quantity:	500

General Information

Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Series:	T428_COTS
Description:	SMD, MnO2, High CV, Molded, COTS, Face Down
Features:	High CV, COTS, Face Down Terminal
RoHS:	No
Termination:	Solder Coated
Notes:	In Polarity Stripe, At KEMET's Option, Type May Be Indicated: FDM= Face Down Terminals T428.

Specifications

Capacitance:	390 uF
Capacitance Tolerance:	10%
Voltage DC:	6.3 VDC (85C), 4.22 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	8%
Failure Rate:	A (Non-ER)
Resistance:	130 mOhms (100kHz 20C)
Leakage Current:	24.6 uAmps (20C)
Testing and Reliability:	Standard Testing Only