

KEMET Part Number: T491C106K016AT
(B45196E3106K309)

Tantalum, MnO₂ Tantalum, T491, 10 uF, 10%, 16 V, 6032, SMD, MnO₂, Molded, 1.8 Ohms, Height Max = 2.8mm



Dimensions

Footprint	6032
L	6mm +/-0.3mm
W	3.2mm +/-0.3mm
H	2.5mm +/-0.3mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.2mm +/-0.1mm
A	2.9mm MIN
B	0.5mm +/-0.15mm
E	2.4mm REF
G	2.8mm REF
P	0.9mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Packaging Specifications

Weight:	224.48 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500

General Information

Dielectric:	MnO ₂ Tantalum
Style:	SMD Chip
Series:	T491
Description:	SMD, MnO ₂ , Molded
RoHS:	Yes
Termination:	Tin

Specifications

Capacitance:	10 uF
Capacitance Tolerance:	10%
Voltage DC:	16 VDC (85C), 10.72 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	6% 120Hz 20C
Failure Rate:	N/A
Resistance:	1.8 Ohms (100kHz)
Current:	247 mAmps (100kHz 25C), 222.3 mAmps (85C), 98.8 mAmps (125C)
Leakage Current:	1.6 uAmps (5min 20C)