

**KEMET Part Number: T491C157K010AT**  
(B45196H2157K309)

Tantalum, MnO<sub>2</sub> Tantalum, T491, 150 uF, 10%, 10 V, 6032, SMD, MnO<sub>2</sub>, Molded, 900 mOhms, Height Max = 2.8mm



General Information	
<b>Dielectric:</b>	MnO <sub>2</sub> Tantalum
<b>Style:</b>	SMD Chip
<b>Series:</b>	T491
<b>Description:</b>	SMD, MnO <sub>2</sub> , Molded
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin

Specifications	
<b>Capacitance:</b>	150 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	10 VDC (85C), 6.7 VDC (125C)
<b>Temperature Range:</b>	-55/+125C
<b>Dissipation Factor:</b>	10% 120Hz 20C
<b>Failure Rate:</b>	N/A
<b>Resistance:</b>	0.9 Ohms (100kHz)
<b>Current:</b>	350 mAmps (100kHz 25C), 315 mAmps (85C), 140 mAmps (125C)
<b>Leakage Current:</b>	15 uAmps (5min 20C)

Dimensions	
<b>Footprint</b>	6032
<b>L</b>	6mm +/-0.3mm
<b>W</b>	3.2mm +/-0.3mm
<b>H</b>	2.5mm +/-0.3mm
<b>T</b>	0.13mm REF
<b>S</b>	1.3mm +/-0.3mm
<b>F</b>	2.2mm +/-0.1mm
<b>A</b>	2.9mm MIN
<b>B</b>	0.5mm +/-0.15mm
<b>E</b>	2.4mm REF
<b>G</b>	2.8mm REF
<b>P</b>	0.9mm REF
<b>R</b>	1mm REF
<b>X</b>	0.1mm +/-0.1mm

Packaging Specifications	
<b>Weight:</b>	224.48 mg
<b>Packaging:</b>	T&R, 178mm
<b>Packaging Quantity:</b>	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.