KEMET Part Number: C0805C151K5RACTU

(C0805C151K5RAC7800)



Ceramic, Commercial-(CxxxxC), 150 pF, 10%, 50 V, 0805, X7R, SMD, MLCC, Temperature Stable, Class II



Dimensions	
L	2mm +/-0.2mm
W	1.25mm +/-0.2mm
Т	0.78mm +/-0.10mm
S	0.75mm MIN
В	0.5mm +/-0.25mm

Packaging Specifications	
Packaging:	T&R, 180mm, Paper Tape
Packaging Quantity:	4000

General Information	
Style:	SMD Chip
Series:	Commercial-(CxxxxC)
Chip Size:	0805
Description:	SMD, MLCC, Temperature Stable, Class II
Features:	Temperature Stable, Class II
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours

Specifications		
Capacitance:	150 pF	
Capacitance Tolerance:	10%	
Voltage DC:	50 VDC	
Dielectric Withstanding Voltage:	125 V	
Temperature Range:	-55/+125C	
Temperature Coefficient:	X7R	
Dissipation Factor:	2.5%	
Aging Rate:	3% Loss/Decade Hour	
Insulation Resistance:	100 GOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

