


KEMET Part Number: CK05BX471K
(C052K471K2X5CA)

Ceramic, Military/High Reliability, MIL-11015, 470 pF, 10%, 200 V, BX, N/A, Lead Spacing = 5.08mm



| General Information | |
|--------------------------|--|
| Style: | Radial |
| Series: | MIL-11015 |
| RoHS: | No |
| Termination: | Lead (SnPb) |
| Failure Rate: | N/A |
| Testing and Reliability: | MIL-PRF-11015 |
| Approvals: | MIL-PRF-11015 |
| Notes: | Lead Length Shown Is For Parts Supplied In Bulk, See Packaging Specifications For Lead Lengths When Not Provided In Bulk |

| Dimensions | |
|------------|-------------------------|
| L | 4.83mm +/-0.25mm |
| H | 4.83mm +/-0.25mm |
| T | 2.29mm +/-0.25mm |
| S | 5.08mm +/-0.38mm |
| LL | 31.75mm MIN |
| F | 0.635mm +0.102/-0.051mm |
| G | 1.143mm MAX |
| K | 4.826mm +/-0.254mm |

| Specifications | |
|----------------------------------|-----------|
| Capacitance: | 470 pF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 200 VDC |
| Dielectric Withstanding Voltage: | 500 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | BX |
| Dissipation Factor: | 2.5% |
| Insulation Resistance: | 100 GOhms |

| Packaging Specifications | |
|--------------------------|-----------|
| Packaging: | Bulk, Bag |
| Packaging Quantity: | 100 |