


Tantalum, MnO₂ Tantalum, Commercial Grade, T322, 4.7 uF, 10%, 20 V, 4.5 Ohms



Dimensions

D	2.79mm MAX
L	7.37mm MAX
LL	38.1mm +/-6.35mm
F	0.51mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	250

General Information

Dielectric:	MnO ₂ Tantalum
Style:	Axial
Series:	T322
Description:	Axial, Solid Tantalum, Molded, Military (Non-ER), Low ESR
Features:	Low ESR
RoHS:	Yes
Termination:	Tin
Lead:	Wire Leads, Uninsulated

Specifications

Capacitance:	4.7 uF
Capacitance Tolerance:	10%
Voltage DC:	20 VDC (85C), 16 VDC (125C Surge), 0.2 V (125C Reverse)
Temperature Range:	-55/+125C
Rated Temperature:	85C
Resistance:	4.5 Ohms (100kHz)
Leakage Current:	0.8 uAmps (25C)