


Tantalum, MnO2 Tantalum, Commercial Grade, T322, 15 uF, 10%, 25 V, 2 Ohms



| General Information |   |
|---------------------|---|
| <b>Dielectric:</b>  | MnO2 Tantalum   |
| <b>Style:</b>       | Axial   |
| <b>Series:</b>      | T322  |
| <b>Description:</b> | Axial, Solid Tantalum, Molded, Military (Non-ER), Low ESR |
| <b>Features:</b>    | Low ESR   |
| <b>RoHS:</b>        | Yes   |
| <b>Termination:</b> | Tin   |
| <b>Lead:</b>        | Wire Leads, Uninsulated                                   |

| Dimensions |                  |
|------------|------------------|
| <b>D</b>   | 4.57mm MAX       |
| <b>L</b>   | 10.67mm MAX      |
| <b>LL</b>  | 38.1mm +/-6.35mm |
| <b>F</b>   | 0.51mm +/-0.05mm |

| Packaging Specifications   |           |
|----------------------------|-----------|
| <b>Packaging:</b>          | Bulk, Bag |
| <b>Packaging Quantity:</b> | 100       |

| Specifications                |  |
|-------------------------------|--|
| <b>Capacitance:</b>           | 15 uF  |
| <b>Capacitance Tolerance:</b> | 10%  |
| <b>Voltage DC:</b>            | 25 VDC (85C), 21 VDC (125C Surge), 0.25 V (125C Reverse) |
| <b>Temperature Range:</b>     | -55/+125C  |
| <b>Rated Temperature:</b>     | 85C  |
| <b>Resistance:</b>            | 2 Ohms (100kHz)  |
| <b>Leakage Current:</b>       | 3 uAmps (25C)  |