

Tantalum, Polymer Tantalum, T520, 330 uF, 20%, 6.3 V, 7343, SMD, Polymer, Molded, Low ESR, Non-Combustible, 25 mOhms, Height Max = 3.1mm



**Dimensions**

Footprint		7343
L		7.3mm +/-0.3mm
W		4.3mm +/-0.3mm
H		2.8mm +/-0.3mm
T		0.13mm REF
S		1.3mm +/-0.3mm
F		2.4mm +/-0.1mm
A		3.6mm MIN
B		0.5mm +/-0.15mm
P		0.9mm REF
R		1mm REF
X		0.1mm +/-0.1mm

**Packaging Specifications**

Weight:	434.83 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500

**General Information**

Dielectric:	Polymer Tantalum
Style:	SMD Chip
Series:	T520
Description:	SMD, Polymer, Molded, Low ESR, Non-Combustible
Features:	Low ESR
RoHS:	Yes
Termination:	Tin

**Specifications**

Capacitance:	330 uF
Capacitance Tolerance:	20%
Voltage DC:	6.3 VDC (105C)
Temperature Range:	-55/+105C
Dissipation Factor:	10% 120Hz 25C
Failure Rate:	N/A
Resistance:	25 mOhms (100kHz 25C)
Current:	3000 mAmps (100kHz 45C), 2100 mAmps (85C), 750 mAmps (105C)
Leakage Current:	207.9 uA (5min 25C)