

Tantalum, Polymer Tantalum, T520, 680 uF, 20%, 2.5 V, 7343, SMD, Polymer, Molded, Low ESR, Non-Combustible, 10 mOhms, Height Max = 3.1mm



| General Information | |
|---------------------|--|
| Dielectric: | Polymer Tantalum |
| Style: | SMD Chip |
| Series: | T520 |
| Description: | SMD, Polymer, Molded, Low ESR, Non-Combustible |
| Features: | Low ESR |
| RoHS: | Yes |
| Termination: | Tin |

| Dimensions | |
|------------|-----------------|
| Footprint | 7343 |
| L | 7.3mm +/-0.3mm |
| W | 4.3mm +/-0.3mm |
| H | 2.8mm +/-0.3mm |
| T | 0.13mm REF |
| S | 1.3mm +/-0.3mm |
| F | 2.4mm +/-0.1mm |
| A | 3.6mm MIN |
| B | 0.5mm +/-0.15mm |
| P | 0.9mm REF |
| R | 1mm REF |
| X | 0.1mm +/-0.1mm |

| Specifications | |
|------------------------|---|
| Capacitance: | 680 uF |
| Capacitance Tolerance: | 20% |
| Voltage DC: | 2.5 VDC (105C) |
| Temperature Range: | -55/+105C |
| Dissipation Factor: | 10% 120Hz 25C |
| Failure Rate: | N/A |
| Resistance: | 10 mOhms (100kHz 25C) |
| Current: | 4700 mAmps (100kHz 45C), 3290 mAmps (85C), 1175 mAmps (105C) |
| Leakage Current: | 170 uA (5min 25C) |

| Packaging Specifications | |
|--------------------------|------------|
| Weight: | 434.83 mg |
| Packaging: | T&R, 178mm |
| Packaging Quantity: | 500 |