

Tantalum, Polymer Tantalum, Multi-Anode, T530, 220 uF, 20%, 6.3 V, 7343, SMD, Polymer, Molded, Multiple Anodes, Low ESR, 6 mOhms, Height Max = 3.1mm



**Dimensions**

Dimensions	
Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	2.8mm +/-0.3mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
A	3.6mm MIN
B	0.5mm +/-0.15mm
P	0.9mm REF
R	1mm REF
X	0.1mm +/-0.1mm

**Packaging Specifications**

Weight:	307.51 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500

**General Information**

Dielectric:	Polymer Tantalum
Style:	SMD Chip
Series:	T530
Description:	SMD, Polymer, Molded, Multiple Anodes, Low ESR
Features:	Low ESR
RoHS:	Yes
Termination:	Tin

**Specifications**

Capacitance:	220 uF
Capacitance Tolerance:	20%
Voltage DC:	6.3 VDC (105C), 4.22 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	8% 120Hz 25C
Failure Rate:	N/A
Resistance:	6 mOhms (100kHz 25C)
Current:	6500 mAmps (100kHz 45C), 4550 mAmps (85C), 1625 mAmps (125C)
Leakage Current:	138.6 uA (5min 25C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.