

Tantalum, MnO₂ Tantalum, T495, 100 uF, 10%, 16 V, 7343, SMD, MnO₂, Molded, Low ESR, 125 mOhms, Height Max = 3.1mm



Dimensions

Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	2.8mm +/-0.3mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
A	3.6mm MIN
B	0.5mm +/-0.15mm
E	3.5mm REF
G	3.5mm REF
P	0.9mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Packaging Specifications

Weight:	446.84 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500

General Information

Dielectric:	MnO ₂ Tantalum
Style:	SMD Chip
Series:	T495
Description:	SMD, MnO ₂ , Molded, Low ESR
Features:	Low ESR
RoHS:	No
Termination:	Solder Coated

Specifications

Capacitance:	100 uF
Capacitance Tolerance:	10%
Voltage DC:	16 VDC (85C), 10.72 VDC (125C)
Temperature Range:	-55/+125C
Dissipation Factor:	8% 120Hz 20C
Failure Rate:	N/A
Resistance:	125 mOhms (100kHz)
Current:	1095 mAmps (100kHz 25C), 985.5 mAmps (85C), 438 mAmps (125C)
Leakage Current:	16 uAmps (5min 20C)