


Tantalum, Polymer Tantalum, T545, 470 uF, 20%, 6.3 V, 7343, SMD, Polymer, Molded, Low Profile, HiEnergyDensity, 45 mOhms, Height Max = 1.5mm



General Information	
<b>Dielectric:</b>	Polymer Tantalum
<b>Style:</b>	SMD Chip
<b>Series:</b>	T545
<b>Description:</b>	SMD, Polymer, Molded, Low Profile, HiEnergyDensity
<b>Features:</b>	Low ESR
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin

Dimensions	
<b>Footprint</b>	7343
<b>L</b>	7.3mm +/-0.3mm
<b>W</b>	4.3mm +/-0.3mm
<b>H</b>	1.4mm +/-0.1mm
<b>T</b>	0.13mm REF
<b>S</b>	1.3mm +/-0.3mm
<b>F</b>	2.4mm +/-0.1mm
<b>A</b>	3.8mm MIN
<b>X</b>	0.05mm REF

Specifications	
<b>Capacitance:</b>	470 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	6.3 VDC (85C), 5.26 VDC (105C)
<b>Temperature Range:</b>	-55/+105C
<b>Dissipation Factor:</b>	10% 120Hz 25C
<b>Failure Rate:</b>	N/A
<b>Resistance:</b>	45 mOhms (100kHz 25C)
<b>Current:</b>	2000 mAmps (100kHz 45C), 1400 mAmps (85C), 500 mAmps (105C)
<b>Leakage Current:</b>	296.1 uA (5min 25C)

Packaging Specifications	
<b>Weight:</b>	222.94 mg
<b>Packaging:</b>	T&R, 178mm
<b>Packaging Quantity:</b>	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.