


Varistors, VP, Plastic Encapsulated, 350 V, 275 VAC, 430 V, 710 V, 5 A, 400 A, 13 J, 100 mW



General Information	
Type:	Varistors
Style:	SMD Molded
Series:	VP
Description:	Surface Mount Varistors
Features:	Plastic Encapsulated
Termination:	Nickel Tin
RoHS:	Yes
Approvals:	UL

Dimensions	
Chip Size	3225
L	8mm +/-0.5mm
W	6.3mm +/-0.4mm
H	4.7mm +/-0.3mm
F	3mm +/-0.3mm
B	1.5mm +/-0.3mm
K	2.3mm +/-0.3mm

Specifications	
Voltage DC:	350 VDC (25C)
Voltage AC:	275 VAC
Temperature Range:	-40/+85C
Storage Temperature Range:	-40/+125C
Varistor Voltage:	430 VDC at 1 mAmps
Clamping Voltage:	710 V
Clamping Current:	5 Amps (8/20 us MAX)
Surge Current:	400 Amps (8/20 us MAX)
Energy:	13 J (10/1000 us MAX)
Capacitance:	75 pf (1kHz)

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	1000