

# RJ45 coupling - VS-08-BU/BU-RJ45-F - 1405617

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



RJ45 coupling, Degree of protection: IP20, Number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), Material: Copper alloy, for VS-08 and push-pull panel mounting frames

Freenet insert



## Key Commercial Data

Packing unit	1 STK
GTIN	
GTIN	4046356460057
Weight per Piece (excluding packing)	22.300 g
Custom tariff number	85366990
Country of origin	Germany

## Technical data

### Mechanical characteristics

Number of positions	8
Number of slots	2
Insertion/withdrawal cycles	>= 100
Degree of protection	IP20

### Material data

Housing material	Copper alloy
------------------	--------------

### Electrical characteristics

Number of positions	8
GRP transmission properties	CAT5 (IEC 11801:2002)
Transmission speed	1 Gbps

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
------------	------------------------------------------

# RJ45 coupling - VS-08-BU/BU-RJ45-F - 1405617


## Technical data

### Environmental Product Compliance


	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	-----------------------------------------------------------------------------------------------------

## Drawings

Dimensional drawing




Schematic diagram




RJ45 socket insert, Freenet system


Schematic diagram



Schematic diagram



Schematic diagram



## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440309

# RJ45 coupling - VS-08-BU/BU-RJ45-F - 1405617

## Classifications

### eCl@ss

eCl@ss 8.0	19179290
eCl@ss 9.0	19179290

### ETIM

ETIM 3.0	EC001134
ETIM 4.0	EC001134
ETIM 5.0	EC001134

### UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	31261501
UNSPSC 13.2	43222604

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		B.01742
-----	--	---------

## Accessories

### Accessories

#### Panel mounting frame

Panel mounting frames - VS-PPC-F1-RJ45-MNNA-1C-F - 1405222



RJ45 panel mounting frame, IP67, for push-pull interlocking, metal, with Freenet system, for round mounting cutout, with seal

## RJ45 coupling - VS-08-BU/BU-RJ45-F - 1405617

### Accessories

#### Panel mounting frames - VS-PPC-F1-RJ45-MNNA-1R-F - 1405358



RJ45 panel mounting frame, IP67, for push-pull interlocking, metal, with the Freenet system, for square panel cutout, with grommet, without mounting screws

---

#### Panel mounting frames - VS-A-S-F-IP67 - 1654581



RJ45 panel mounting frame, IP67, irradiated for welding applications, for Freenet system, for round panel cutout, with grommet, without mounting screws

---

#### Panel mounting frames - VS-A-F-IP67 - 1653744



Panel mounting frame, IP67, for Freenet system, for round panel cutout, with grommet, without mounting screws, color: gray

---

#### Panel mounting frames - VS-A-F-IP67-BK - 1658668



Panel mounting frame, IP67, for Freenet system, for round panel cutout, with grommet, without mounting screws, color: black

---

#### Panel mounting frames - VS-PPC-F1-RJ45-POBK-1R-F - 1608197



RJ45 panel mounting frame, IP67, for push-pull interlocking, plastic, with the Freenet system, for square panel cutout, with grommet, without mounting screws

---