

Device connector, front mounting - SH-8ESC58AAC00S - 1621559

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://phoenixcontact.com/download>)




Device connector for front wall, angled rotatable, SPEEDCON locking, M23, Number of positions: 4+4+4+PE, Type of contact: Socket, Crimp connection, Axial O-ring, 4x Ø 3.2, Flange dimensions: 28 mm x 28 mm

Why buy this product

- ✓ Easy connection, thanks to infinitely adjustable cable outlet direction up to 310°
- ✓ Transmission of signals, data, and power in just a single connector
- ✓ CAT5 data interface
- ✓ Safe use in the field, thanks to high degree of protection
- ✓ Consistent EMC protection for reliable connection solutions in the industrial environment



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 937078
GTIN	4046356937078
Weight per Piece (excluding packing)	139.500 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Temperature range

Ambient temperature (operation)	-40 °C ... 130 °C
---------------------------------	-------------------

Data of the insulating body

Note	Order information: Crimp contacts, 4x Ø 0.8 mm, 4x Ø 1 mm, 5x Ø 2 mm, order separately
Coding	N
Insulator material	Polyamide (PA 6.6)
Insertion/withdrawal cycles mechanical	100

Device connector, front mounting - SH-8ESC58AAC00S - 1621559

Technical data

Data of the insulating body

Contact connection method	Crimp connection
Type of contacts	Socket
Number of positions	13
Contact diameter of power contacts	2 mm
Litz wire cross section of power contacts min.	0.25 mm ²
Litz wire cross section of power contacts max.	4 mm ²
Nominal current per power contact at 25°C	30 A
Nominal voltage, power contact	630 V AC
	850 V DC
Rated surge voltage	6 kV
Contact diameter of signal contacts	1 mm
Litz wire cross section of signal contacts min.	0.06 mm ²
Litz wire cross section of signal contacts max.	1 mm ²
Nominal current per signal contact at 25°C	8 A
Nominal voltage, signal contact	50 V
Rated surge voltage	1.5 kV
Contact diameter, data contacts	0.8 mm
Litz wire cross section, data contacts, min.	0.08 mm ²
Litz wire cross section, data contacts, max.	0.5 mm ²
Nominal current per data contact at 25°C	3.6 A
Nominal voltage of data contact	50 V
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing data

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Flange dimensions	28 mm x 28 mm
Type of locking	SPEEDCON locking
Degree of protection (when plugged in)	IP67
	IP68
Thread type	M23


Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings


Device connector, front mounting - SH-8ESC58AAC00S - 1621559

Schematic diagram




Socket pin assignment, CAT5

Dimensional drawing



Pin version: dimension A = 4.7 mm, socket version: dimension A = 0 mm

Dimensional drawing



Installation dimensions

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440102
eCl@ss 9.0	27440103

ETIM

ETIM 4.0	EC002635
ETIM 5.0	EC002635
ETIM 6.0	EC002635

UNSPSC

UNSPSC 13.2	39121413
-------------	----------

Approvals

Approvals

Device connector, front mounting - SH-8ESC58AAC00S - 1621559


Approvals

Approvals

cULus Recognized / EAC

Ex Approvals

Approval details

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E468743-20150928
Nominal current I _N	16 A	
Nominal voltage U _N	600 V	

EAC		B.01742
-----	---	---------

Accessories

Accessories

Crimp contact

Crimp contact - SF-08KS010 - 1621571



Crimp contact, turned, Contact diameter: 0.8 mm, Crimp range: 0.08 mm²...0.25 mm²

Crimp contact - SF-08KS020 - 1621573



Crimp contact, turned, Contact diameter: 0.8 mm, Crimp range: 0.34 mm²...0.5 mm²

Device connector, front mounting - SH-8ESC58AAC00S - 1621559

Accessories

Crimp contact - ST-10KS010 - 1618239



Crimp contact, turned, Single contact, Contact diameter: 1 mm, Crimp range: 0.06 mm²...0.25 mm²

Crimp contact - ST-10KS020 - 1618251



Crimp contact, turned, Single contact, Contact diameter: 1 mm, Crimp range: 0.34 mm²...0.5 mm²

Crimp contact - ST-10KS030 - 1618254



Crimp contact, turned, Single contact, Contact diameter: 1 mm, Crimp range: 0.5 mm²...1 mm²

Crimp contact - SF-20KS021 - 1621576



Crimp contact, turned, Contact diameter: 2 mm, Crimp range: 0.25 mm²...1 mm²

Crimp contact - SF-20KS022 - 1621577



Crimp contact, turned, Contact diameter: 2 mm, Crimp range: 1.5 mm²...2.5 mm²

Device connector, front mounting - SH-8ESC58AAC00S - 1621559

Accessories

Crimp contact - SF-20KS023 - 1621578



Crimp contact, turned, Contact diameter: 2 mm, Crimp range: 2.5 mm²...4 mm²

Mounting material

Color-coding - RF-Z0017 - 1620624



Color-coding, Color: green

Color-coding - RF-Z0018 - 1620625



Color-coding, Color: orange

Color-coding - RF-Z0019 - 1620626



Color-coding, Color: black

Protective cover

Plastic dust protection cap - SH-Z2304 - 1622137



Plastic dust protection cap for M23 hybrid connectors with external thread

Device connector, front mounting - SH-8ESC58AAC00S - 1621559

Accessories

Metal dust protection cap - SH-Z2303 - 1622138



Metal dust protection cap for M23 hybrid connectors with external thread

Metal dust protection cap - SH-Z2302 - 1622139



Metal dust protection cap with steel wire for M23 hybrid connectors with external thread

Sample set - M23 HYBRID_CONTACT-SAMPLE-SET - 1623252

Sample set consisting of 4 x Ø 1.0 mm, 4 x Ø 0.8 mm, 5 x Ø 2.0 mm for all socket and pin contacts for M23 hybrid connectors. Contacts included: 1621573, 1618254, 1621577, 1621575, 1618261, 1621580