

**Productname :** LEAK DETECTOR  
**Ref.Nr.:** BDS001563\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 4.0  
**Replaces:** BDS001563\_20160929

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**LEAK DETECTOR**  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Gas leak detector

### 1.3. Details of the supplier of the safety data sheet

**CRC Industries UK Ltd.**  
**Ambersil House - Wylds Road**  
**Castlefield Industrial Estate**  
**TA6 4DD Bridgwater Somerset**  
**United Kingdom**  
**Tel.: +44 1278 727200**  
**Fax.: +44 1278 425644**  
**E-mail : hse.uk@crcind.com**

### 1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No 1272/2008

**Physical:** Aerosol, category 3  
Pressurised container: May burst if heated.  
Classification is based on test data.

**Health:** Eye irritation, category 2  
Causes serious eye irritation.  
Classification based on calculation method.

**Environment:** Not classified  
Classification based on calculation method.

### 2.2. Label elements

#### Labelling according to Regulation (EC) No 1272/2008



**Productname :** LEAK DETECTOR  
**Ref.Nr.:** BDS001563\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 4.0  
**Replaces:** BDS001563\_20160929

**Hazard pictogram(s):**

<b>Signal word:</b>	Warning
<b>Hazard statement(s):</b>	H229 : Pressurised container: May burst if heated. H319 : Causes serious eye irritation.
<b>Precautionary statement(s):</b>	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P251 : Do not pierce or burn, even after use. P280-2 : Wear eye protection/face protection. P337/313 : If eye irritation persists: Get medical advice/attention. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.
<b>Supplemental Hazard information:</b>	Contains: 1,2-benzisothiazol-3(2H)-one May produce an allergic reaction.

**2.3. Other hazards**

No information available

**SECTION 3: Composition/information on ingredients****3.1. Substances**

Not applicable.

**3.2. Mixtures**

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
2-amino-2-methylpropanol	01-2119475788-16	124-68-5	204-709-8	<1	Eye Irrit. 2, Skin Irrit. 2, Aquatic Chronic 3	H319,H315,H412	B
Amines, C12-14 (even numbered)- alkyldimethyl, N-oxides	01-2119490061-47	-	(931-292-6)	<1	Eye Dam. 1, Acute Tox. 4, Skin Irrit. 2, Aquatic Acute 1, Aquatic Chronic 2	H318,H302,H315,H400,H411	Q
dinitrogen oxide	01-2119970538-25	10024-97-2	233-032-0	<2.5	Ox. Gas 1, Press. Gas	H270,H280	B,W
(Z)-N-methyl-N-(1-oxo-9-octadecenyl)glycine	01-2119488991-20	110-25-8	203-749-3	<2.5	Acute Tox. 4, Skin Irrit. 2, Eye Dam. 1, Aquatic Acute 1	H332,H315,H318,H400	B
1,2-benzisothiazol-3(2H)-one	-	2634-33-5	220-120-9	<0.05	Acute Tox. 4, Skin Irrit. 2, Eye Dam. 1, Skin Sens. 1, Aquatic Acute 1	H302,H315,H318,H317,H400	X

**Explanation notes**

B : substance with national established workplace exposure limit

Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

W : Note: substance mentioned on the list of CMR-substances of the Dutch Ministry of Social Affairs and Employment (SZW)

**Productname :** LEAK DETECTOR  
**Ref.Nr.:** BDS001563\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 4.0  
**Replaces:** BDS001563\_20160929

X : SCL (specific concentration limit) in accordance with art.10 of CLP Regulation No 1272/2008

(\* Explanation phrases : see chapter 16)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
<b>Contact with skin :</b>	Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
<b>Inhalation :</b>	Fresh air, keep warm and at rest.
<b>Ingestion :</b>	If swallowed accidentally, do not induce vomiting and seek medical advice.

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	No harmful effects known if used for its intended purpose
<b>Ingestion :</b>	no special hazards known - LD50 oral rat > 5000 mg/kg
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	Irritating to eyes Symptoms : redness and pain

### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures



3 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** LEAK DETECTOR  
**Ref.Nr.:** BDS001563\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 4.0  
**Replaces:** BDS001563\_20160929

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.  
Eyewash bottles should be available

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep out of reach of children.

### 7.3. Specific end use(s)

Gas leak detector

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

**Productname :** LEAK DETECTOR  
**Ref.Nr.:** BDS001563\_3\_20170629 (EN) **Creationdate :** 29.06.17 Version : 4.0  
**Replaces:** BDS001563\_20160929

**Exposure limits :**

Hazardous ingredient	CAS-nr.	method	
<b>National established exposure limits, United Kingdom</b>			
dinitrogen oxide	10024-97-2	TWA	100 ppm

**8.2. Exposure controls**

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. In all cases handle and use the product in accordance with good industrial hygiene practices. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A)
<b>hands and skin :</b>	For incidental contact with the product wear chemical-resistant gloves (standard EN 374). The use of disposable gloves is acceptable provided that they are changed immediately after a splash or spill. Where intentional contact is expected reusable gloves with a breakthrough time of minimum 10 minutes should be used. The breakthrough time of the glove has to be adapted to the total duration of product use. In all cases handle and use the product in accordance with good industrial hygiene practices.
Recommended gloves:	Nitrile
<b>eyes :</b>	Wear safety eyewear according to EN 166.
<b>Environmental protection:</b>	Avoid release to the environment. Collect spillage.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	N2O propelled liquid.
<b>colour :</b>	Colorless.
<b>odour :</b>	Neutral.
<b>pH :</b>	7.76
<b>Boiling point/range :</b>	Not available.
<b>Flash point :</b>	None
<b>Evaporation rate :</b>	Not available.
<b>Explosion limits : upper limit :</b>	Not available.
<b>lower limit :</b>	Not available.
<b>Vapour pressure :</b>	Not available.
<b>Relative density :</b>	0.999 g/cm <sup>3</sup> (@ 20°C).
<b>Solubility in water :</b>	Soluble in water
<b>Auto-ignition :</b>	> 200 °C

**Productname :** LEAK DETECTOR  
**Ref.Nr.:** BDS001563\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 4.0  
**Replaces:** BDS001563\_20160929

## 9.2. Other information

VOC = volatile organic compounds 0 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO2

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

<b>acute toxicity:</b>	based on available data the classification criteria are not met
<b>skin corrosion/irritation:</b>	based on available data the classification criteria are not met
<b>serious eye damage/irritation:</b>	Causes serious eye irritation.
<b>respiratory or skin sensitisation:</b>	based on available data the classification criteria are not met
<b>germ cell mutagenicity:</b>	based on available data the classification criteria are not met
<b>carcinogenicity:</b>	based on available data the classification criteria are not met
<b>toxicity for reproduction:</b>	based on available data the classification criteria are not met
<b>STOT-single exposure:</b>	based on available data the classification criteria are not met
<b>STOT repeated exposure:</b>	based on available data the classification criteria are not met
<b>aspiration hazard:</b>	based on available data the classification criteria are not met

Information on likely routes of exposure:



6 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylids Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** LEAK DETECTOR  
**Ref.Nr.:** BDS001563\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 4.0  
**Replaces:** BDS001563\_20160929

**Inhalation :** No harmful effects known if used for its intended purpose  
**Ingestion :** no special hazards known - LD50 oral rat > 5000 mg/kg  
**Skin contact :** May produce an allergic reaction.  
**Eye contact :** Causes serious eye irritation.

**Toxicological data :**

Hazardous ingredient	CAS-nr.	method	
(Z)-N-methyl-N-(1-oxo-9-octadecenyl)glycine	110-25-8	LD50 oral rat	9200 mg/kg
Amines, C12-14 (even numbered)- alkyldimethyl, N-oxides	-	LD50 oral rat	1064 mg/kg

**SECTION 12: Ecological information****12.1. Toxicity**

Not classified

**Ecotoxicological data:**

Hazardous ingredient	CAS-nr.	method	
(Z)-N-methyl-N-(1-oxo-9-octadecenyl)glycine	110-25-8	IC50 algae	5.1 mg/l
		LC50 fish	3.2-4.6 mg/l
		EC50 daphnia	0.53 mg/l
Amines, C12-14 (even numbered)- alkyldimethyl, N-oxides	-	IC50 algae	0.143 mg/l
		LC50 fish	2.67 mg/l
		EC50 daphnia	3.1 mg/l

**12.2. Persistence and degradability**

No experimental data available

**12.3. Bioaccumulative potential**

No experimental data available

**12.4. Mobility in soil**

Soluble in water

**12.5. Results of PBT and vPvB assessment**

No information available

**12.6. Other adverse effects**

No experimental data available



7 / 9

**CRC Industries UK Limited**  
 Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
 Somerset, TA6 4DD  
 Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** LEAK DETECTOR  
**Ref.Nr.:** BDS001563\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 4.0  
**Replaces:** BDS001563\_20160929

GWP (global warming potential): 3

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.

**National regulations :** Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : 1950

### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

### 14.3. Transport hazard class(es)

Class: 2.2  
Subsidiary risk: 5.1  
ADR/RID - Classification code: 5O

### 14.4. Packing group

Packing group: Not applicable.

### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (E)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code



8 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com



**Productname :** LEAK DETECTOR  
**Ref.Nr.:** BDS001563\_3\_20170629 (EN)

**Creationdate :** 29.06.17 Version : 4.0  
**Replaces:** BDS001563\_20160929

Not applicable.

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

### 15.2. Chemical safety assessment

No information available

## SECTION 16: Other information

\*Explanation hazard statements: H270 : May cause or intensify fire; oxidiser.  
H280 : Contains gas under pressure; may explode if heated.  
H302 : Harmful if swallowed.  
H315 : Causes skin irritation.  
H317 : May cause an allergic skin reaction.  
H318 : Causes serious eye damage.  
H319 : Causes serious eye irritation.  
H332 : Harmful if inhaled.  
H400 : Very toxic to aquatic life.  
H411 : Toxic to aquatic life with long lasting effects.  
H412 : Harmful to aquatic life with long lasting effects.

REVISIONS IN CHAPTRE : 8.2. Exposure controls

acronyms and synonyms: TWA = time weight average  
STEL = short time exposure limit  
VOC = volatile organic compounds  
PBT = persistant bioaccumulative toxic  
vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.