

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Sensor/actuator flush-type connector, socket, 4-pos. M8, rear/screw mounting with M10 fastening thread, with angled solder connection

### Why buy this product

- Standard pin assignments and codings for signal transmission with a uniform design-in design
- For high transmission reliability: optional shield connection to the housing and latching on the PCB



## **Key Commercial Data**

Packing unit	20 STK
Minimum order quantity	20 STK
GTIN	4 046356 605731
GTIN	4046356605731
Weight per Piece (excluding packing)	7.220 g
Custom tariff number	85366990
Country of origin	Germany

#### Technical data

#### Ambient conditions

Ambient temperature (operation)	-25 °C 85 °C
Degree of protection	IP67

### General

Rated current at 40°C	4 A
Rated voltage	50 V AC
	60 V DC
Number of positions	4
Insulation resistance	$\geq$ 100 M $\Omega$
Coding	A - standard



## Technical data

### General

Standards/regulations	M8 connector IEC 61076-2-104
Status display	No
Overvoltage category	II
Degree of pollution	3
Connection method	Solder pins
Torque	1 Nm (Installation-side)
Mounting type	Rear mounting With flat nut

#### Material

Flammability rating according to UL 94	НВ	
Contact material	Cu alloy	
Contact surface material	Au	
Contact carrier material	PA 66	
Material, knurls	Zinc die-cast, nickel-plated	
Sealing material	NBR	

#### Cable

Standards/specifications	M8 connector IEC 61076-2-104
Ambient temperature (operation)	-25 °C 85 °C

## Standards and Regulations


Standard designation	M8 connector
Standards/regulations	IEC 61076-2-104
Flammability rating according to UL 94	НВ

## **Environmental Product Compliance**

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings

### Dimensional drawing



### Schematic diagram




Pin assignment M8 socket, 4-pos., view female side

Mounting panel with feed-through hole




Drilling diagram



### Dimensional drawing





Drilling diagram

M8 flush-type socket

## Classifications

### eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27440103
eCl@ss 9.0	27440102

### **ETIM**

ETIM 4.0	EC002061
ETIM 5.0	EC002061
ETIM 6.0	EC002061

## UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	39121413

## Approvals

## Approvals

Approvals

EAC

Ex Approvals



## Approvals

Approval details

EAC EAC	B.01742
---------	---------

Phoenix Contact 2017 © - all rights reserved http://www.phoenixcontact.com