

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Sensor/actuator flush-type connector, plug, 5-pos., DeviceNet, M8, rear/screw mounting with M10 fastening thread, with angled solder connection

## Why buy this product

- For high transmission reliability: optional shield connection to the housing and latching on the PCB



## **Key Commercial Data**

Packing unit	20 STK
GTIN	4 046356 712521
GTIN	4046356712521
Weight per Piece (excluding packing)	6.790 g
Custom tariff number	85366990
Country of origin	Germany

## Technical data

#### Ambient conditions

Ambient temperature (operation)	-25 °C 85 °C
Degree of protection	IP67

#### General

Rated current at 40°C	3 A
Rated voltage	30 V AC
	30 V DC
Number of positions	5
Insulation resistance	≥ 100 MΩ
Coding	B - inverse
Standards/regulations	M8 connector IEC 61076-2-104
Status display	No



## Technical data

## General

Overvoltage category	II
Degree of pollution	3
Connection method	Solder pins
Mounting type	Rear mounting M8 x 1 With flat nut

#### Material

Flammability rating according to UL 94	НВ
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PA 66
Material, knurls	Zinc die-cast, nickel-plated

#### Cable

Standards/specifications	M8 connector IEC 61076-2-104
--------------------------	------------------------------

## Standards and Regulations


Standard designation	M8 connector
Standards/regulations	IEC 61076-2-104
Flammability rating according to UL 94	НВ

## **Environmental Product Compliance**

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## **Drawings**

#### Dimensional drawing



## Schematic diagram




Pin assignment M8 plug, 5-pos., B-coded, view plug side

Housing cutout for M8 flush-type connector, connector, one-section



## Drilling diagram



Drilling diagram

## Classifications

## eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27440103
eCl@ss 9.0	27440102

## **ETIM**

ETIM 3.0	EC002061
ETIM 4.0	EC002635
ETIM 5.0	EC002061
ETIM 6.0	EC002061

## **UNSPSC**

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	39121413

## **Approvals**

Approvals

Approvals

EAC

Ex Approvals



Approvals		
Approval details		
EAC	EAC	B.01742

Phoenix Contact 2017 © - all rights reserved http://www.phoenixcontact.com