

# ALUMINUM ELECTROLYTIC CAPACITORS



Chip Type, For Audio Equipment  
Wide Temperature Range



- Chip type acoustic series within the wide temperature range.
- Applicable to automatic mounting machine fed with carrier tape.
- Compliant to the RoHS directive (2011/65/EU)



## Specifications



| Item                          | Performance Characteristics   |                 |                    |    |    |    |   |
|-------------------------------|---|-----------------|--------------------|----|----|----|---|
| Category Temperature Range    | -40 to +105°C   |                 |                    |    |    |    |   |
| Rated Voltage Range           | 6.3 to 50V  |                 |                    |    |    |    |   |
| Rated Capacitance Range       | 0.1 to 1000μF   |                 |                    |    |    |    |   |
| Capacitance Tolerance         | ±20% (120Hz, 20°C)  |                 |                    |    |    |    |   |
| Leakage Current               | After 1 minute's application of rated voltage at 20°C, leakage current is not more than 0.03 CV or 4 (μA), whichever is greater.  |                 |                    |    |    |    |   |
| Tangent of loss angle (tan δ) | Measurement frequency : 120Hz at 20°C   |                 |                    |    |    |    |   |
|                               | Rated voltage (V)   | 6.3             | 10                 | 16 | 25 | 35 | 50  |
| Stability at Low Temperature  | Measurement frequency : 120Hz   |                 |                    |    |    |    |   |
|                               | Impedance ratio   | Z-25°C / Z+20°C | 4                  | 3  | 2  | 2  | 2   |
|                               | ZT / Z20 (MAX.)   | Z-40°C / Z+20°C | 8                  | 5  | 4  | 3  | 3   |
| Endurance                     | The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 1000 hours at 105°C.  |                 | Capacitance change |    |    |    | Within ±20% of the initial capacitance value      |
|                               |   |                 | tan δ              |    |    |    | 200% or less than the initial specified value     |
| Shelf Life                    | After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above. |                 | Leakage current    |    |    |    | Less than or equal to the initial specified value |
|                               |   |                 | Capacitance change |    |    |    | Within ±10% of the initial capacitance value      |
| Resistance to soldering heat  | The capacitors are kept on a hot plate for 30 seconds, which is maintained at 250°C. The capacitors shall meet the characteristic requirements listed at right when they are removed from the plate and restored to 20°C.               |                 | tan δ              |    |    |    | Less than or equal to the initial specified value |
|                               |   |                 | Leakage current    |    |    |    | Less than or equal to the initial specified value |
| Marking                       | Black print on the case top.  |                 |                    |    |    |    |   |

## Chip Type


(φ4 to φ6.3)

Voltage (j:6.3V)

Lot No.





## Type numbering system (Example : 6.3V 100μF)



(φ8 × 6.2L)

Voltage (A : 10V)

Trade mark





| φD × L | 4 × 5.4    | 5 × 5.4    | 6.3 × 5.4  | 8 × 6.2    | 8 × 10     | 10 × 10    |
|--------|------------|------------|------------|------------|------------|------------|
| A      | 1.8        | 2.1        | 2.4        | 3.3        | 2.9        | 3.2        |
| B      | 4.3        | 5.3        | 6.6        | 8.3        | 8.3        | 10.3       |
| C      | 4.3        | 5.3        | 6.6        | 8.3        | 8.3        | 10.3       |
| E      | 1.0        | 1.3        | 2.2        | 2.3        | 3.1        | 4.5        |
| L      | 5.4        | 5.4        | 5.4        | 6.2        | 10         | 10         |
| H      | 0.5 to 0.8 | 0.5 to 0.8 | 0.5 to 0.8 | 0.5 to 0.8 | 0.8 to 1.1 | 0.8 to 1.1 |

(φ8 × 10L, φ10 × 10L)

Voltage (V : 35V)

Trade mark



### Rated voltage

| V    | 6.3 | 10 | 16 | 25 | 35 | 50 |
|------|-----|----|----|----|----|----|
| Code | j   | A  | C  | E  | V  | H  |

● Dimension table in next page.



## ■ Dimensions

| Cap. (μF) | Code | V         |           | 6.3        |           | 10        |           | 16        |     | 25        |     | 35        |     | 50                       |                 |
|-----------|------|-----------|-----------|------------|-----------|-----------|-----------|-----------|-----|-----------|-----|-----------|-----|--------------------------|-----------------|
|           |      | 0J        | 1A        | 1C         | 1E        | 1V        | 1H        |           |     |           |     |           |     |                          |                 |
| 0.1       | 0R1  |           |           |            |           |           |           |           |     |           |     |           |     | 4 × 5.4                  | 1.0             |
| 0.22      | R22  |           |           |            |           |           |           |           |     |           |     |           |     | 4 × 5.4                  | 2.6             |
| 0.33      | R33  |           |           |            |           |           |           |           |     |           |     |           |     | 4 × 5.4                  | 3.2             |
| 0.47      | R47  |           |           |            |           |           |           |           |     |           |     |           |     | 4 × 5.4                  | 3.8             |
| 1         | 010  |           |           |            |           |           |           |           |     |           |     |           |     | 4 × 5.4                  | 6.2             |
| 2.2       | 2R2  |           |           |            |           |           |           |           |     |           |     |           |     | 4 × 5.4                  | 11              |
| 3.3       | 3R3  |           |           |            |           |           |           |           |     |           |     |           |     | 4 × 5.4                  | 14              |
| 4.7       | 4R7  |           |           |            |           |           |           |           |     |           |     |           |     | 4 × 5.4                  | 15              |
| 10        | 100  |           |           | 4 × 5.4    | 22        | 4 × 5.4   | 18        | 5 × 5.4   | 23  | 5 × 5.4   | 25  | 6.3 × 5.4 | 30  | 5 × 5.4                  | 19              |
| 22        | 220  | 4 × 5.4   | 22        | 5 × 5.4    | 27        | 5 × 5.4   | 30        | 6.3 × 5.4 | 38  | 6.3 × 5.4 | 42  | 8 × 6.2   | 51  | 8 × 6.2                  | 30              |
| 33        | 330  | 5 × 5.4   | 30        | 5 × 5.4    | 35        | 6.3 × 5.4 | 40        | 6.3 × 5.4 | 48  | 8 × 6.2   | 59  | 8 × 10    | 140 | 8 × 10                   | 140             |
| 47        | 470  | 5 × 5.4   | 36        | 6.3 × 5.4  | 46        | 6.3 × 5.4 | 50        | 8 × 6.2   | 66  | 8 × 10    | 155 | 8 × 10    | 180 | 8 × 10                   | 180             |
| 100       | 101  | 6.3 × 5.4 | 60        | ○6.3 × 5.4 | 60 (90)   | ●8 × 6.2  | 102 (210) | 8 × 10    | 155 | 10 × 10   | 300 | 10 × 10   | 220 | 10 × 10                  | 220             |
| 220       | 221  | ●8 × 6.2  | 102 (210) | ●8 × 6.2   | 102 (210) | △8 × 10   | 210 (310) | 10 × 10   | 300 | 10 × 10   | 300 |           |     |                          |                 |
| 330       | 331  | ●8 × 6.2  | 102 (210) | △8 × 10    | 210 (310) | △8 × 10   | 210 (310) |           |     |           |     |           |     |                          |                 |
| 470       | 471  | △8 × 10   | 210 (310) | △8 × 10    | 210 (310) | △8 × 10   | 210 (310) |           |     |           |     |           |     |                          |                 |
| 1000      | 102  | 10 × 10   | 310       |            |           |           |           |           |     |           |     |           |     | Case size<br>φD × L (mm) | Rated<br>ripple |

Size φ8 × 6.2L is available for capacitors marked "○".

Size φ8 × 10L is available for capacitors marked "●".

Size φ10 × 10L is available for capacitors marked "△".

※ In this case, [6] will be put at 12th digit of type numbering system.

Rated ripple current (mArms) at 105°C 120Hz

## ● Frequency coefficient of rated ripple current

| Frequency   | 50 Hz | 120 Hz | 300 Hz | 1 kHz | 10 kHz or more |
|-------------|-------|--------|--------|-------|----------------|
| Coefficient | 0.70  | 1.00   | 1.17   | 1.36  | 1.50           |

- Taping specifications are given in page 23.
- Recommended land size, soldering by reflow are given in page 18, 19.
- Please refer to page 3 for the minimum order quantity.