


Ceramic, 200C, MoldedHighTemp, 0.1 uF, 10%, 50 V, COG, High Temp, 200C, Radial Molded, Gold Termination, Industrial Grade, Lead Spacing = 5.08mm



General Information	
Style:	Radial
Series:	MoldedHighTemp
Description:	High Temp, 200C, Radial Molded, Gold Termination, Industrial Grade
Features:	Commercial
RoHS:	With Exemptions
Termination:	Gold
Halogen Free:	Yes

Dimensions	
L	4.83mm +/-0.25mm
H	5.97mm +/-0.25mm
T	2.29mm +/-0.25mm
S	5.08mm +/-0.38mm
LL	31.75mm MIN
F	0.635mm +0.102/-0.051mm
G	1.14mm MAX
K	4.83mm +/-0.25mm

Specifications	
Capacitance:	0.1 uF
Capacitance Tolerance:	10%
Voltage DC:	50 VDC
Dielectric Withstanding Voltage:	250 V
Temperature Range:	-55/+200C
Temperature Coefficient:	COG
Dissipation Factor:	2.5%
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	10 GOhms

Packaging Specifications	
Weight:	493 mg
Packaging:	T&R, 305mm
Packaging Quantity:	500