

SPECIFICATIONS

SAMPLE NO.: 55-1853



CUSTOMERS NO.: JOB NO.:

DATE: 2002/03/14


ITEMS:	SPECIFICATION:	VOICE COIL:
Dimensions	105mm (4")	Diameter 25.4 (mm)
Impedance	8ohms	Length 9.1 (mm)
Input	RATED MAX 30W	Layer 2 (mm)
Free air resonance	60 ±12Hz	Former material Aluminum
Sensitivity	86 ± 2dB/W/M, 2.83V	Wire material Copper
Frequency range	Fo~ 17000Hz	MAGNET: (1) (2)
Sine wave test	6.3V	Diameter 72 70 (mm)
Weight	890grams	Height 15 10 (mm)
Life test	15w, 8H , EIA white noise	Weight 245 152 (g)
		Gap(H) 4 (mm)

PARAMETERS:

DC resistance	Re: 6.8 (Ω)	Moving mass	Mms: 5.83 (g)
Resonance frequency	Fs: 59.59 (Hz)	Equivalent volume	Vas: 5.0 (l)
Maximum impedance	Zm: 38.4 (Ω)	Sensitivity	SPL: 86.26 (dB)
Mechanical Q factor	Qms: 2.41	Suspension compliance	Cms: 1.22 (mm/N)
Electrical Q factor	Qes: 0.46	BL product	Bl: 5.67 (N/A)
Total Q factor	Qts: 0.38	Driver piston diameter	D: 83 (mm)
Linear Displacement	Xmax: 2.55 (mm)	Voice Coil Inductance	Le: 0.77 (mH)



DESIGN	CHARGE	HEAD	MANAGER
--------	--------	------	---------



1/0 1/3

K	一般公差	MATERIAL	SCALE	QUANTITY
	ISSUE	REVISIONS	DATE	NAME
IN.			FINISH	TOLERANCE ANGLE
				±
AW.			TITLE	4" SPEAKER
			初版發行	55-1853
1			94.11.04	部