




See Color In Almost Complete Darkness Without IR LEDs

HTINTB8G	2.8 - 12mm auto iris varifocal lens, dark grey housing
HTINTB8GW	2.8 - 12mm auto iris varifocal lens, white housing
HTINTB10G	9 - 22mm auto iris varifocal lens, dark grey housing
HTINTB10GW	9 - 22mm auto iris varifocal lens, white housing

Features

- 650 lines of color resolution
- Amplify existing light with no distance limitations
- No problems caused by objects that reflect or absorb IR light sources
- Automatic thermostatic sensor
- Minimum illumination 0.00002 lux (Intensifier3™ @ 512x)
- Dual voltage 12VDC & 24VAC operation
- Full OSD operation
- -40° with Glacier™ heaters
- External controls for zoom & focus
- Weather resistant operation
- EZ mount system simplifies installation
- 5 year warranty




Now with Presets:
 Outdoor, Indoor, Elevator,
 Lobby, Hallway & Dark

Specifications

Image Sensor.....	1/3" Sony Super-HAD II™ CCD	Speco DNR.....	On / Off (level adjustable)
Resolution.....	650 TV lines	Digital Zoom.....	On / Off (1x - 16x)
Minimum Illumination.....	CDS Off: 0.15 lux CDS On: 0.00002 lux	DIS.....	On / Off
Total Pixels.....	811 (H) x 508 (V)	Sharpness.....	On / Off (level adjustable)
Effective Pixels.....	768 (H) x 494 (V)	Flip / Mirror.....	On / Off
TV System.....	NTSC	Power Consumption.....	12VDC, 250mA (heater off) 800mA (heater on) 24VAC, 100mA (heater off) 380mA (heater on)
Scanning Frequency.....	15.734kHz (H) / 59.94Hz (V)	Power Supply.....	12VDC / 24VAC dual voltage operation (power supply not included)
Scanning System.....	2:1 interlace	Operating Temperature/ Humidity.....	14° F – 122° F / RH 95% max. - 40° F with Glacier™ heaters
Synchronization.....	Internal	Storage Temperature/ Humidity.....	- 4° F – 140° F / RH 95% max.
S/N Ratio.....	More than 52dB	Dimensions.....	3.46" (W) x 3.43" (H) x 11.22" (D)
Video Output.....	CVBS: 1.0Vp-p / 75 Ohms	Weight.....	3 lbs.
Electronic Shutter Speed.....	1/60 sec. – 1/120,000 sec.		
OSD.....	Available		
WDR.....	On / Off (level adjustable)		
Backlight Compensation.....	BLC / HLC / Off		
Day & Night.....	Color / BW / Auto		
Gain Control.....	High / Low / Off		
White Balance.....	ATW / Outdoor / Indoor / Manual / AWC (1,700°K - 11,000°K)		
Intensifier3™.....	Auto / Off (selectable 2x - 512x)		
Motion Detection.....	On / Off (8 programmable zones)		
Privacy Masking.....	On / Off (12 programmable zones)		

Optional Accessories



Speco Technologies is constantly developing and improving products.
 We reserve the right to modify product design and specifications without notice and without incurring any obligation.



Rev. 2/13/12