

KEMET Part Number: C1206C225K8RACTU
(C1206C225K8RAC7800)

Ceramic, SMD Comm X7R, 2.2 uF, 10%, 10 V, 1206, X7R, SMD, MLCC, Temperature Stable, Class II



Dimensions

| | |
|----------|-----------------|
| L | 3.2mm +/-0.2mm |
| W | 1.6mm +/-0.2mm |
| T | 1.6mm +/-0.20mm |
| B | 0.5mm +/-0.25mm |

Packaging Specifications

| | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 2000 |

General Information

| | |
|-----------------------|--|
| Style: | SMD Chip |
| Series: | SMD Comm X7R |
| Chip Size: | 1206 |
| Description: | SMD, MLCC, Temperature Stable, Class II |
| Features: | Temperature Stable, Class II |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Failure Rate: | N/A |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 48 hours |

Specifications

| | |
|---|---------------------|
| Capacitance: | 2.2 uF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 10 VDC |
| Dielectric Withstanding Voltage: | 25 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | X7R |
| Dissipation Factor: | 5% 120Hz 25C |
| Aging Rate: | 3% Loss/Decade Hour |
| Insulation Resistance: | 227 MOhms |