


Tantalum, MnO2 Tantalum, Commercial Grade, T322, 1 uF, 10%, 35 V, 8 Ohms



General Information	
<b>Dielectric:</b>	MnO2 Tantalum
<b>Style:</b>	Axial
<b>Series:</b>	T322
<b>Description:</b>	Axial, Solid Tantalum, Molded, Military (Non-ER), Low ESR
<b>Features:</b>	Low ESR
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Lead:</b>	Wire Leads, Uninsulated

Dimensions	
<b>D</b>	2.79mm MAX
<b>L</b>	7.37mm MAX
<b>LL</b>	38.1mm +/-6.35mm
<b>F</b>	0.51mm +/-0.05mm

Packaging Specifications	
<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	250

Specifications	
<b>Capacitance:</b>	1 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	35 VDC (85C), 28 VDC (125C Surge), 0.35 V (125C Reverse)
<b>Temperature Range:</b>	-55/+125C
<b>Rated Temperature:</b>	85C
<b>Resistance:</b>	8 Ohms (100kHz)
<b>Leakage Current:</b>	0.5 uAmps (25C)