

For more Information
please call

1-800-Belden1



General Description:

22 AWG stranded (7x30) TC conductors, polypropylene insulation, paper wrap, twisted pair, overall Beldfoil shield (100% coverage), 22 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	22	7x30	TC - Tinned Copper

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PP - Polypropylene	.008

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	7x30	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.138 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +75°C
Bulk Cable Weight:	15 lbs/1000 ft.
Max. Recommended Pulling Tension:	27 lbs.
Min. Bend Radius/Minor Axis:	1.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
45

Nom. Inductance:

Inductance (µH/ft)
.17

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
34

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
67

Nominal Velocity of Propagation:

VP (%)
66

Nominal Delay:

Delay (ns/ft)
1.5

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
14.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
14.1

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.9 Amps per conductor @ 25°C

Notes (Overall)

Notes: Unique paper separator facilitates jacket stripping.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8451 008U1000	1,000 FT	16.000 LB	GRAY		2 #22 PP SHLD PVC FR
8451 008U500	500 FT	8.500 LB	GRAY		2 #22 PP SHLD PVC FR
8451 0081000	1,000 FT	16.000 LB	GRAY	C	2 #22 PP SHLD PVC FR
8451 008500	500 FT	8.000 LB	GRAY		2 #22 PP SHLD PVC FR
8451 010U1000	1,000 FT	16.000 LB	BLACK		2 #22 PP SHLD PVC FR
8451 010U500	500 FT	8.500 LB	BLACK		2 #22 PP SHLD PVC FR
8451 010100	100 FT	2.200 LB	BLACK		2 #22 PP SHLD PVC FR
8451 0101000	1,000 FT	16.000 LB	BLACK	C	2 #22 PP SHLD PVC FR
8451 01010000	10,000 FT	160.000 LB	BLACK		2 #22 PP SHLD PVC FR
8451 01015000	15,000 FT	240.000 LB	BLACK		2 #22 PP SHLD PVC FR
8451 010500	500 FT	8.000 LB	BLACK		2 #22 PP SHLD PVC FR
8451 0105000	5,000 FT	80.000 LB	BLACK		2 #22 PP SHLD PVC FR

Notes:

C = CRATE REEL PUT-UP.

8451 Multi-Conductor - Single-Pair Cable

Revision Number: 1 Revision Date: 07-30-2013

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).