


Tantalum, MnO2 Tantalum, Commercial Grade, T350, 33 uF, 10%, 25 V, Radial, Solid Tantalum, Conformal, Dipped, Lead Spacing = 5.08mm



General Information	
<b>Dielectric:</b>	MnO2 Tantalum
<b>Style:</b>	Radial
<b>Series:</b>	T350
<b>Description:</b>	Radial, Solid Tantalum, Conformal, Dipped
<b>Features:</b>	Low Leakage
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Notes:</b>	Longest Lead Is Positive

Dimensions	
<b>D</b>	8.4mm
<b>H</b>	12.7mm
<b>S</b>	5.08mm +/-0.38mm
<b>LL</b>	12.7mm +/-1.26mm
<b>F</b>	0.5mm +/-0.05mm

Specifications	
<b>Capacitance:</b>	33 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	25 VDC (85C), 21 VDC (125C Surge), 0.25 V (125C Reverse)
<b>Temperature Range:</b>	-55/+125C
<b>Dissipation Factor:</b>	6%
<b>Leakage Current:</b>	6.6 uAmps

Packaging Specifications	
<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	100

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.