

8418 Multi-Conductor - Microphone/Musical Instrument Cable



For more Information please call

1-800-Belden1



General Description:

Mic, 20 AWG stranded (26x34) high-conductivity TC conductors, rubber insulation, cotton wrap, rayon braid, TC braid shield (85% coverage), EPDM rubber jacket.

braid, TO braid shield (0570 coverage), ET DR			
Physical Characteristics (Overall)			
Conductor AWG:			
# Conductors AWG Stranding Conductor Material	Dia. (in.)		
8 20 26x34 High Conductivity TC - Tinned Cor	pper .037		
Total Number of Conductors:	8		
Insulation			
Insulation Material:			
	ss (in.) Dia. (in.)		
EPDM - Ethylene Propylene Diene Monomer Rubber 023	.083		
Outer Shield Outer Shield Material:			
Type Outer Shield Material Coverage (%)			
Braid TC - Tinned Copper 85			
Outer Jacket			
Outer Jacket Material:			
Outer Jacket Material Nom. Wall Th	ickness (in.)		
EPDM - Ethylene Propylene Diene Monomer Rubber .037			
Overall Cable Overall Cabling Color Code Chart:			
Number Color			
1 Blue			
2 Orange			
3 Black			
4 White 5 Brown			
5 Brown 6 Green			
7 Red			
8 Yellow			
Overall Cabling Separator Material:	Rayon Braid, Cotton Serve		
Overall Nominal Diameter:	0.381 in.		
Machanical Characteristics (Overall)			
Mechanical Characteristics (Overall) Operating Temperature Range:			
	-50°C To +90°C		
Non-UL Temperature Rating:	00°C		
Bulk Cable Weight:	100 lbs/1000 ft.		
Max. Recommended Pulling Tension:	116 lbs.		
Min. Bend Radius/Minor Axis:	3.800 in.		
Applicable Specifications and Agency Compliance (Overall)			
Applicable Standards & Environmental Programs			
EU Directive 2011/65/EU (ROHS II):	Yes		
EU CE Mark:	Yes		
EU Directive 2000/53/EC (ELV):	Yes		
EU Directive 2002/95/EC (RoHS):	Yes		
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004		

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

8418 Multi-Conductor - Microphone/Musical Instrument Cable

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Plenum/Non-Plenum	
Plenum (Y/N):	No
Electrical Characteristics (Overall)	
Nom. Characteristic Impedance:	
Impedance (Ohm) 52	
Nom. Inductance:	
Inductance (μH/ft) 0.18	
Nom. Capacitance Conductor to Conductor:	
Capacitance (pF/ft) 30	
Nom. Capacitance Cond. to Other Conductor & Shield:	
Capacitance (pF/ft) 55	
Nom. Conductor DC Resistance:	
DCR @ 20°C (Ohm/1000 ft) 10.2	
Nominal Outer Shield DC Resistance:	
DCR @ 20°C (Ohm/1000 ft) 2.4	
Max. Operating Voltage - Non-UL:	
Voltage 600 V RMS	
Max. Recommended Current:	
Current 2.8 Amps per conductor @ 25°C	
Put line and Calana	

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8418 010100	100 FT	11.000 LB	BLACK		8 #20 EPDM BRD EPDM
8418 010250	250 FT	26.750 LB	BLACK	С	8 #20 EPDM BRD EPDM

Notes:

C = CRATE REEL PUT-UP.

Revision Date: 08-13-2012 Revision Number: 1

© 2017 Belden, Inc All Rights Reserved

All hough Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).