


8450 Multi-Conductor - Single-Pair Cable



For more Information
please call

1-800-Belden1

**General Description:**

22 AWG solid tinned copper conductors, polypropylene insulation, twisted pair, overall Beldfoil shield (100% coverage), 22 AWG solid TC drain wire, PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	22	Solid	TC - Tinned Copper

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PP - Polypropylene	.007

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	Solid	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.018

Overall Cable

Overall Nominal Diameter: 0.118 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +105°C
UL Temperature Rating:	75°C
Bulk Cable Weight:	12 lbs/1000 ft.
Max. Recommended Pulling Tension:	37 lbs.
Min. Bend Radius/Minor Axis:	1.250 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
EU Directive 2011/65/EU (RoHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes

8450 Multi-Conductor - Single-Pair Cable

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MIL Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 UL Loading

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

40

Nom. Inductance:

Inductance (µH/ft)

0.08

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

40

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

76

Nominal Velocity of Propagation:

VP (%)

66

Nominal Delay:

Delay (ns/ft)

1.5

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

16.1

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

12.65

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

2.9 Amps per conductor @ 25°C

Notes (Overall)

Notes: Belden's® Miniature Type Broadcast Audio and Instrumentation Cables occupy 1/2 to 2/3 less space than standard cables.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8450 0081000	1,000 FT	13.000 LB	GRAY		2 #22 PP SHLD PVC FR
8450 010U1000	1,000 FT	14.000 LB	BLACK		2 #22 PP SHLD PVC FR
8450 010U500	500 FT	7.500 LB	BLACK		2 #22 PP SHLD PVC FR
8450 0101000	1,000 FT	13.000 LB	BLACK		2 #22 PP SHLD PVC FR

Revision Number: 1 Revision Date: 08-27-2012

© 2017 Belden, Inc
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).



8450 Multi-Conductor - Single-Pair Cable