



For more Information
please call

1-800-Belden1



General Description:

20 AWG stranded (7x28) bare copper conductors, foam HDPE insulation, overall Beldfoil® shield (100% coverage) plus tinned copper braid shield (78% coverage), 22 AWG stranded (19x34) tinned copper drain wire, PVC jacket.

Usage (Overall)

Suitable Applications: CC Link

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
3	20	7x28	BC - Bare Copper

Total Number of Conductors: 3

Insulation

Insulation Material:

Insulation Material
FHDPE - Foam High Density Polyethylene

Insulation Color Code Chart:

Number	Color
1	Blue
2	Yellow
3	White

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	78

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	19x34	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.035

Overall Cable

Overall Nominal Diameter: 0.303 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +60°C

Bulk Cable Weight: 49 lbs/1000 ft.

Max. Recommended Pulling Tension: 46 lbs.

Min. Bend Radius/Minor Axis: 3 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CM

CEC/C(UL) Specification: CM

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

1348A Multi-Conductor - CC Link Certified Cable

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	08/15/2006
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	Mitsubishi CC Link Signal

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

110

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

18.3

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

9.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

8

Max. Operating Voltage - UL:

Voltage

300 V RMS

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1348A 0021000	1,000 FT	53.000 LB	RED	C	3 #20 FPE SH PVC
1348A 0025000	5,000 FT	270.000 LB	RED	C Z	3 #20 FPE SH PVC

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 02-12-2009

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).