

## 1035A Multi-Conductor - 300V Power-Limited Tray Cable



For more Information  
please call

1-800-Belden1



### General Description:

16 AWG pairs stranded (7x24) bare copper conductors, twisted pairs, PVC insulation, unshielded, PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	16	7x24	BC - Bare Copper

Total Number of Conductors: 2

#### Insulation

Insulation Material:

Insulation Material
PVC - Polyvinyl Chloride

#### Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.037

Outer Jacket Ripcord: Yes

#### Overall Cable

Overall Nominal Diameter: 0.258 in.

#### Pair

Pair Color Code Chart:

Number	Color
1	Black & White

### Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

Bulk Cable Weight: 36.400 lbs/1000 ft.

Max. Recommended Pulling Tension: 71.400 lbs.

Min. Bend Radius/Minor Axis: 2.600 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 105°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes

## 1035A Multi-Conductor - 300V Power-Limited Tray Cable

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

### Flame Test

UL Flame Test: UL1685 FT4 Loading

CSA Flame Test: FT4

IEEE Flame Test: 1202

### Suitability

Sunlight Resistance: Yes

### Plenum/Non-Plenum

Plenum (Y/N): No

### Surface Printing (Overall)

### Electrical Characteristics (Overall)

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

3.7

#### Max. Operating Voltage - UL:

Voltage

300 V RMS

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1035A 0101000	1,000 FT	38.000 LB	BLACK	C	2 #16 PVC PVC
1035A 01010000	10,000 FT	380.000 LB	BLACK	C Z	2 #16 PVC PVC

#### Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 3 Revision Date: 05-17-2015

© 2016 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).