

XCSLF3737333

metal safety switch XCSLF-4NC+2NO- slow
break - 3 entries tapped 1/2" NPT - 120V



Main

Range of product	Preventa Safety detection
Product or component type	Safety switch
Component name	XCSLF
Design	Slim
Material	Metal
Head type	Key operated turret head
Contacts type and composition	2 NC + 1 NO
Contacts operation	Slow-break, break before make
Solenoid contacts type and composition	2 NC + 1 NO (slow-break, break before make)
Cable entry	3 entries tapped 1/2" NPT
Electromagnet interlocking	Locking on de-energisation and unlocking on energisation of solenoid
[Us] rated supply voltage	120 V (- 15...10 %)
Electrical connection	Spring terminal, 1 x 1.5 mm ² flexible or solid cable Spring terminal, 2 x 0.5 mm ² flexible cables with 13 mm bared ends
Number of poles	3
Locking options description	With interlocking, locking by solenoid
Local signalling	1 LED orange (actuator withdrawn) 1 LED green (actuator inserted and locked)
Signalling circuit voltage	120 V

Complementary

Positive opening	With NC contact
Supply voltage type	AC/DC
Supply frequency	50/60 Hz
Load factor	1
Signalling circuit type	AC
Mechanical durability	1000000 cycles

Minimum actuation speed	0.01 m/s
Maximum actuation speed	0.5 m/s
[Ie] rated operational current	0.55 A at 24 V utilisation category DC-13, R300 conforming to EN/IEC 60947-5-1 0.75 A at 240 V utilisation category AC-15, C300 conforming to EN/IEC 60947-5-1
[Ithe] conventional enclosed thermal current	4 A
Maximum load current	<= 15 A
[Ui] rated insulation voltage	300 V conforming to CSA C22.2 No 14 250 V (degree of pollution: 3) conforming to EN/IEC 60947-1 300 V conforming to UL 508
[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 60947-5-1
Minimum switching current	10 mA at 20 °C
Minimum switching voltage	17 V
Short circuit protection	4 A cartridge fuse type gG (gl) 6 A type fast blow
Actutr forcible withdrawal rtc	<= 3000 N
Actuator force for extraction	>= 20 N
Resistance to mechanical impact	9.6 J against the partition 6.4 J without partition
Operating rate	10 cyc/mn for maximum durability
Safety level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 conforming to EN/IEC 61508
Safety reliability data	B10d = 5500000 (value given for a life time of 20 years limited by mechanical or contact wear)
Body material	Zamak
Head material	Zamak
Depth	51 mm
Height	205 mm
Width	44 mm
Product weight	1.1 kg

Environment

Standards	EN 1088/ISO 14119 CSA C22.2 No 14 EN/ISO 13849-1 UL 508 EN/IEC 60204-1 EN/IEC 60947-5-1 EN/IEC 62061
Product certifications	CSA TÜV UL
Protective treatment	TC
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	5 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	10 gn for 11 ms conforming to IEC 60068-2-27
Class of protection against electric shock	Class I conforming to EN/IEC 60536
IP degree of protection	IP66 conforming to EN/IEC 60529 and EN/IEC 60947-5-1 IP67

Contractual warranty

Warranty period	18 months
-----------------	-----------