

## Device connector, front mounting - SH-8ESC58AWA00S - 1621567

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Device connector for front wall, straight, shielded: yes, Screw locking, M23, Number of positions: 4+4+4+PE, Type of contact: Socket, Crimp connection, Axial O-ring, 4x Ø 3.2, Flange dimensions: 26 mm x 26 mm

### Why buy this product

- Transmission of signals, data, and power in just a single connector
- CAT5 data interface
- Safe use in the field, thanks to high degree of protection
- Consistent EMC protection for reliable connection solutions in the industrial environment

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 937153
GTIN	4046356937153
Weight per Piece (excluding packing)	48.600 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Temperature range

Ambient temperature (operation)	-40 °C ... 130 °C
---------------------------------	-------------------

#### Data of the insulating body

Note	Order information: Crimp contacts, 4x Ø 0.8 mm, 4x Ø 1 mm, 5x Ø 2 mm, order separately
Coding	N
Insulator material	Polyamide (PA 6.6)
Insertion/withdrawal cycles mechanical	100
Contact connection method	Crimp connection

## Device connector, front mounting - SH-8ESC58AWA00S - 1621567

### Technical data

#### Data of the insulating body

Type of contacts	Socket
Number of positions	13
Contact diameter of power contacts	2 mm
Litz wire cross section of power contacts min.	0.25 mm <sup>2</sup>
Litz wire cross section of power contacts max.	4 mm <sup>2</sup>
Nominal current per power contact at 25°C	30 A
Nominal voltage, power contact	630 V AC
	850 V DC
Rated surge voltage	6 kV
Contact diameter of signal contacts	1 mm
Litz wire cross section of signal contacts min.	0.06 mm <sup>2</sup>
Litz wire cross section of signal contacts max.	1 mm <sup>2</sup>
Nominal current per signal contact at 25°C	8 A
Nominal voltage, signal contact	50 V
Rated surge voltage	1.5 kV
Contact diameter, data contacts	0.8 mm
Litz wire cross section, data contacts, min.	0.08 mm <sup>2</sup>
Litz wire cross section, data contacts, max.	0.5 mm <sup>2</sup>
Nominal current per data contact at 25°C	3.6 A
Nominal voltage of data contact	50 V
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing data

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Flange dimensions	26 mm x 26 mm
Type of locking	Screw locking
Degree of protection (when plugged in)	IP67
	IP68
Thread type	M23


#### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


### Drawings

# Device connector, front mounting - SH-8ESC58AWA00S - 1621567

Schematic diagram




Dimensional drawing



Socket pin assignment, CAT5

Pin version: dimension A = 4.75 mm, socket version: dimension A = 0 mm

Dimensional drawing



Installation dimensions

## Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440102
eCl@ss 9.0	27440103

ETIM

ETIM 4.0	EC002635
ETIM 5.0	EC002635
ETIM 6.0	EC002635

UNSPSC

UNSPSC 13.2	39121413
-------------	----------

## Approvals

Approvals

# Device connector, front mounting - SH-8ESC58AWA00S - 1621567

## Approvals

Approvals

cULus Recognized / EAC

Ex Approvals

## Approval details

cULus Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> E468743-20150928
Nominal current I <sub>N</sub>	16 A	
Nominal voltage U <sub>N</sub>	600 V	

EAC		B.01742
-----	--	---------

## Accessories

Accessories

Crimp contact

Crimp contact - SF-08KS010 - 1621571



Crimp contact, turned, Contact diameter: 0.8 mm, Crimp range: 0.08 mm<sup>2</sup>...0.25 mm<sup>2</sup>

Crimp contact - SF-08KS020 - 1621573



Crimp contact, turned, Contact diameter: 0.8 mm, Crimp range: 0.34 mm<sup>2</sup>...0.5 mm<sup>2</sup>

## Device connector, front mounting - SH-8ESC58AWA00S - 1621567

### Accessories

Crimp contact - ST-10KS010 - 1618239



Crimp contact, turned, Single contact, Contact diameter: 1 mm, Crimp range: 0.06 mm<sup>2</sup>...0.25 mm<sup>2</sup>

---

Crimp contact - ST-10KS020 - 1618251



Crimp contact, turned, Single contact, Contact diameter: 1 mm, Crimp range: 0.34 mm<sup>2</sup>...0.5 mm<sup>2</sup>

---

Crimp contact - ST-10KS030 - 1618254



Crimp contact, turned, Single contact, Contact diameter: 1 mm, Crimp range: 0.5 mm<sup>2</sup>...1 mm<sup>2</sup>

---

Crimp contact - SF-20KS021 - 1621576



Crimp contact, turned, Contact diameter: 2 mm, Crimp range: 0.25 mm<sup>2</sup>...1 mm<sup>2</sup>

---

Crimp contact - SF-20KS022 - 1621577



Crimp contact, turned, Contact diameter: 2 mm, Crimp range: 1.5 mm<sup>2</sup>...2.5 mm<sup>2</sup>

---

## Device connector, front mounting - SH-8ESC58AWA00S - 1621567

### Accessories

Crimp contact - SF-20KS023 - 1621578



Crimp contact, turned, Contact diameter: 2 mm, Crimp range: 2.5 mm<sup>2</sup>...4 mm<sup>2</sup>

---

### Mounting material

Color-coding - RF-Z0017 - 1620624



Color-coding, Color: green

---

Color-coding - RF-Z0018 - 1620625



Color-coding, Color: orange

---

Color-coding - RF-Z0019 - 1620626



Color-coding, Color: black

---

### Protective cover

Plastic dust protection cap - SH-Z2304 - 1622137



Plastic dust protection cap for M23 hybrid connectors with external thread

---

## Device connector, front mounting - SH-8ESC58AWA00S - 1621567

### Accessories

Metal dust protection cap - SH-Z2303 - 1622138



Metal dust protection cap for M23 hybrid connectors with external thread

---

Metal dust protection cap - SH-Z2302 - 1622139



Metal dust protection cap with steel wire for M23 hybrid connectors with external thread

---

Sample set - M23 HYBRID\_CONTACT-SAMPLE-SET - 1623252

Sample set consisting of 4 x Ø 1.0 mm, 4 x Ø 0.8 mm, 5 x Ø 2.0 mm for all socket and pin contacts for M23 hybrid connectors. Contacts included: 1621573, 1618254, 1621577, 1621575, 1618261, 1621580

---

---