
Pomona®

Model 6262 Test Probe Adapter Extended Fine Point



FEATURES:

- Test tip adapter has been designed to IEC 1010, which is the latest international safety standard.
- Snaps onto Pomona's DMM Probes with .080" (2 mm) O.D. Tips.
- Pin tip jack at the adapter end is recessed for added insulation protection
- Adapter allows access to hard to reach test points.
- Tip is insulated to the point to prevent shorting of adjacent components.

MATERIALS:

Tip: Stainless Steel
Tip Insulation: Kynar

Body: Polypropylene, Fire Retardant, UL94 V-2 Rated, Color: One Red, One Black

RATING:

IEC 1010-2-031, Category II, P2 Compliant

Operating Voltage: 300 VRMS/DC

Current: 3 Amperes.

ORDERING INFORMATION: Model 6262-*

* =Color: -0 Black and -2 Red

Extended Tip Adapter is also included in many of Pomona's DMM Test Accessory Kits

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02$ " (,51 mm), $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

7/8/02 SY/EH/LS

I ast saved by Laura Goldberg

Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060

Pomona*ACCESS* **90459** (800) 444-6785 or (425) 446-6010 More drawings available at www.pomonaelectronics.com